


# Modular Jack

154-7616C

KOBICONN

Modular Jack



Dimensions: In.

SPECIFICATIONS	
Type:	USOC Modular Handset
Leads:	4" PVC Insulated
Color:	Gray
Contacts:	Phosphor Bronze 6 Micron Gold Plated
Housing:	ABS Resin
Wire:	28 AWG, 7 Strands 300V
Insulation:	PVC
Insulation Resistance:	10MΩ min.
Contact Resistance:	20mΩ max.
Dielectric Strength:	1000Vrms @ 60Hz
Insertion Force:	500g
Retention Strength:	7.7kgs Between Jack and Plug
Crimp Tensile Strength:	2.27kgs

Date Last Revised: 10-15-05

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300602

154-7616C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-7616C](#)