



Part No.	463-473	Item No.	MDJ8DS	Customer Code:	C3110
Edited By:	Angel	Check By:		Approved by:	Minghu

Standard Specification

REVISIONS				
DATE	REV.	ZONE	DESCRIPTION	ECN NO.
2008/01/17	A		NEW RELEASE	
2008/04/09	B		Revise Part no.	
2008/05/16	C		Revise Part no.	
08/13/2012	D	All	Revised second source	1208008

P.C.B. EDGE (TOP VIEW)



SCALE 4:1

SPECIFICATIONS:

Electrical:

Current Rating:100V AC 1A MAX. 12V DC 2A MAX.

Insulation Resistance:500MΩ MIN. at 500V DC

Dielectric Strength:500V AC/1 minute

Contact Resistance:30 mΩ MAX.

Mechanical:

Insertion Force:4.5KG MAX.

Withdrawal Force:0.9KG ~3.0 KG

Contact Retention Force:1.02KG MIN.

RoHS

5	BACK SHIELDING	1	BS H=0.35t NIKEL PLATE
4	CONNECTOR	3~8	BS H=0.5t Sn PLTE
3	EARTH	1	BS H=0.4t NICKEL PLATE
2	COVER	1	PBT UL94V-0 100%新料
1	BODY	1	PBT UL94V-0 100%新料
P/N	PART NAME	Q' TY	MATERIAL

UNLESS OTHERWISE SPECIFIED TOLERANCE: ANGLES: ±2°		TITLE MINI DIN SOCKET 8 Pin			
X.XX ±0.3 X.XX ±0.15 DO NOT SCALE DRAWING		DRAWN BY Angel		C3110	
CHECKED BY		SIZE A		UNIT mm	
APPROVED BY Minghu		SCALE 2:1		PART NO. 463-473	
DWG NO.		THIRD ANGLE PROJECTION		PAGE 1 OF 1	
		ITEM NO. MDJ8DS-01		DATE 08/13/2012	