


GENERAL PURPOSE SNAP ACTION



Retail Part No.	Bulk Part No.	Fig. No.	Amps **VAC	Amps 125 VDC	Amps 250 VDC	HP 125 VAC	HP 250 VAC	PT Max. (In)	OT Min. (In)	DT Max. (In)	OF Max. Oz. (grams)	Actuator	Actuator Length (In)	Terminal Type	Spec Drawing Page No.
35-461	35-461-BU	1	15			3/4	1-1/2	0.050	0.050	0.010	20 (567)	PI		QC .250"	269-A
35-462	35-462-BU	2	15			3/4	1-1/2	0.050	0.187	0.010	20 (567)	PI w/OT		QC .250"	269-B
35-463	35-463-BU	3	15			3/4	1-1/2	0.281	0.062	0.094	20 (567)	Ro	1.50	QC .250"	269-C
35-464	35-464-BU	4	15			3/4	1-1/2	0.312	0.187	0.062	20 (567)	Lever	2.50	QC .250"	269-D
35-830	35-830-BU	5	15			3/4	1-1/2	0.050	0.050	0.010	20 (567)	Red Pb		QC .250"	269-E
35-831	35-831-BU	5	15			3/4	1-1/2	0.050	0.050	0.010	20 (567)	Black Pb		QC .250"	269-E
35-990	35-990-BU	6	15			3/4	1-1/2	0.050	0.050	0.010	30 (850)	PI		QC .250"	269-F
35-992	35-992-BU	7	15			3/4	1-1/2	0.312	0.187	0.062	30 (850)	Lever	2.50	QC .250"	269-F
35-3900	35-3900-BU	8	15			1/8	1/4	0.020	0.005	0.002	13 (370)	PP		Sc	269-G
35-3901	35-3901-BU	8	15	1/2	1/4			0.016	0.005	0.002	12.3 (350)	PP		Sc	269-G
35-3907	35-3907-BU	9	15					0.158	0.063	0.002	5.3 (151)	LRO	1.783	Sc	269-O
35-3910	35-3910-BU	10	20	1/2	1/4	1	2	0.028	0.140	0.008	22.9 (650)	RP		Sc	269-I
35-3911	35-3911-BU	10	15					0.016	0.140	0.002	12.3 (349)	RP		Sc	269-I
35-828	35-828-BU	11	20	1/2	1/4	1	2	0.156	0.062	0.050	5-13 (142-370)	LL	1.95	Sd/Sc	269-H
35-829	35-829-BU	11	15	1/2	1/4	1	2	0.156	0.062	0.050	5-13 (142-370)	LL	1.97	Sd	269-H
35-890	35-890-BU	12	20	1/2	1/4			0.380	0.190	0.156	3.5-26 (100-740)	Lever	2.50	Sc	269-J
35-892	35-892-BU	13	20	1/2	1/4	1	2	0.020	0.055	0.002	12.3 (350)	SP		Sd/Sc	269-K&L
35-894	35-894-BU	14	20	1/2	1/4	1	2	0.020	0.005	0.002	12.3 (350)	PP		Sd/Sc	269-L
35-896	35-896-BU	15	20	1/2	1/4	1	2	0.020	0.063	0.002	12.3 (350)	PI w/OT		Sd/Sc	269-M
35-980	35-980-BU	14	20	1/2	1/4			0.030	0.005	0.005	26 (740)	PP		Sd/Sc	269-L
35-982	35-982-BU	15	20	1/2	1/4			0.030	0.220	0.005	26 (740)	PI		Sd/Sc	269-M
35-984	35-984-BU	12	20	1/2	1/4			0.380	0.190	0.047	2.5-9 (60-255)	Lever	2.50	Sd/Sc	269-J
35-987	35-987-BU	16	20	1/2	1/4	1/2	1	0.468	0.062	0.085	3.5 (100)	Ro	1.91	Sc	269-N
35-3903	35-3903-BU	13	20	1/2	1/4	3/4	1 1/2	0.020	0.055	0.002	12.3 (350)	SP		Sc	269-K
35-3904	35-3904-BU	17	20	1/2	1/4	1	2	0.158	0.062	0.050	5.3 (150)	LL	1.95	Sc	269-H
35-3906	35-3906-BU	16	20	1/2	1/4	1	2	0.156	0.062	0.050	5-13 (142-370)	LRO	1.78	Sc	269-O

Notes: All of the above have momentary action
 **125/250VAC
 All but 35-990 & 35-992 (DPDT) have SPDT

DT=Differential Travel
 HP=Horse Power
 HRO=Hinged Roller
 LRO=Leaf Rollers
 LL=Leaf Lever

OF=Operating Force
 OT=Over Travel
 Pb=Pushbuttons
 PI=Plunger

PT=Pre-Travel
 QC=Quick Connect
 RP=Roller Plunger
 Sc=Screw

Sd=Solder
 ShRo=Short Roller
 SP=Stub Plunger
 PP=Pin Plunger
 Ro=Roller

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.