

CABLE INTERFACE ACCESSORIES

Optocouplers




Type	OS 24 VDC Optocoupler pluggable
Part No.	112490
Input Voltage	24 VDC±10%
Output Voltage	5...48 VDC
Output Current	0.1 A
Spare Optocoupler for	822420, 822421, 822424, 822425, 822431, 822437

Type	OS 24 VDC/2 A Optocoupler pluggable
Part No.	117020
Input Voltage	24 VDC ±10%
Output Voltage	24 VDC ±10%
Output Current	2.0 A
Spare Optocoupler for	822432

Type	OS 24 VDC Optocoupler pluggable
Part No.	115300
Input Voltage	24 VDC ±10%
Output Voltage	250 VAC
Output Current	0.1 A
Spare Optocoupler for	822433

Relays



Type	24 VDC Relay pluggable
Part No.	413879
Input Voltage	24 VDC
Contact Material	AgCuNi
Spare Relay for	822418, 822419, 822430

Type	24 VDC Relay pluggable
Part No.	403656
Input Voltage	24 VDC
Contact Material	AgNi 5µm Au Plated
Spare Relay for	822422, 822423

Prepared Flat Strip Round Cable



The flat strip round cable is equipped at both ends with 10, 26 or 40 pin plug-in connectors. This cable connects the PLC front panel adapters to the passive or active PLC input/output modules.



Technical Data	
Rated Voltage	300 V
Current Carrying Capacity per Wire	1 A
Total Current Carrying Capacity	
- 40 Pin Cable	26 A/ΔT = 20 K
- 10 Pin Cable	11.5 A/ΔT = 20 K
Rated Cross-Section Wire	0.14 mm²
Resistance Value	55 mΩ/m
Storage temperature	-10 ... +80°C

Type	Length	Part No.
FBK 10/100 RK	1.00 m	823536
FBK 10/150 RK	1.50 m	823537
FBK 10/200 RK	2.00 m	823538
FBK 10/250 RK	2.50 m	823539
FBK 10/300 RK	3.00 m	823540
FBK 10/350 RK	3.50 m	823541
FBK 10/400 RK	4.00 m	823542
FBK 10/450 RK	4.50 m	823543
FBK 10/500 RK	5.00 m	823544
FBK 40/100 RK	1.00 m	821635
FBK 40/150 RK	1.50 m	821636
FBK 40/200 RK	2.00 m	821637
FBK 40/250 RK	2.50 m	821638
FBK 40/300 RK	3.00 m	821639
FBK 40/350 RK	3.50 m	821640
FBK 40/400 RK	4.00 m	821641
FBK 40/450 RK	4.50 m	823534
FBK 40/500 RK	5.00 m	823535
FBK 26/100	1.00 m	998163
FBK 26/200	2.00 m	998164
FBK 26/300	3.00 m	998165

OKI Flex Cable



Item/Type	20 terminals	40 terminals
Ribbon Cable	Conductors: 7/0.127 mm (AWG 28)	
Power Supply	Conductors: 21/0.18 mm (AWG 20)	
Sheath	10.3 mm	12.0 mm
Rated Voltage	150 V	
Rated Current	1 A	

Type	Length	Part No.
OK 20 PLC Cable	1.00 m	993067-1
OK 20 PLC Cable	2.00 m	993067-2
OK 20 PLC Cable	3.00 m	993067-3
IOK 20-1 / IZUMI	1.00 m	993124-1
IOK 20-1.5 / IZUMI	1.50 m	993124-1.5
40 Pin Fijitsu OKIFLEX	1.00 m	990359-1
40 Pin Fijitsu OKIFLEX	2.00 m	990359-2
40 Pin Fijitsu OKIFLEX	3.00 m	990359-3