



2.5mm Stereo Jack

161-3304

KOBICONN

2.5mm Stereo Jack



Dimensions: mm (IN.)

SPECIFICATIONS

Housing:	LCP black UL94V-0
Terminals:	Phosphor bronze silver plated
Tip terminals:	Cu alloy silver plated
Insertion/ Ext. force:	.3-3 Kgs
Dielectric strength:	250 VAC for 1 min.
Insulation resistance:	100 M ohm minimum
Contact resistance:	50 m ohm maximum
Life cycle:	5000 mating minimum
Operating temperature:	-25°C to +85°C
Voltage rating:	16.0 VDC
Current Rating:	0.3 A

Date Last Revised: 4-4-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300405

161-3304

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3304](#)