

PRODUCT DATASHEET



TUF2AAPE

BRIGHT

- Three White LEDs deliver 20 lumens of light



TOUGH

- Survives a 4-meter drop
- Rugged ABS, steel and rubber construction
- Shatterproof lens



RELIABLE

- Pushbutton switch is designed to last a lifetime
- LEDs never need replacing



WEATHERPROOF

- Meets IEC 60529 IPX4 standards for water resistance



The Toughest Flashlight You'll Ever Need™. Perfect for close-up jobs, the Energizer® Hard Case Professional® LED Task Light is always at hand and ready to perform. The compact size makes the light easy to carry and store. An anti-roll design combined with impact resistance greatly reduces the potential for damage to internal components. A shatterproof lens protects the LEDs from harsh environments. In addition, this light keeps your cost of ownership low with an impressive 30-hour run time.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Energizer Hard Case Professional LED Task Light
Model:	TUF2AAPE
Color:	Black and Dark Grey
Power Source:	Two "AA"
ANSI / NEDA:	15 Series
Lamp:	Three Nichia® LEDs
Lamp Life (hr):	Lifetime
Lamp Output (lumens):	20
Beam Distance (m):	38
Peak Beam Intensity (cd):	380
Run Time (h:mm):	30
Durability:	Survives a 4-meter drop
Typical Weight:	114 grams without batteries
Dimensions (mm):	172 x 44.5

Performance:



Tested according to ANSI / NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved