

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0439152005

Status:

Inactive

Description:

10.00mm (.394") Pitch Mini-Fit Sr.™ Header, Dual Row, Vertical, Surface Mount
Compatible, with Solderable Retention Clip, 14 Circuits



Documents:

Drawing (PDF)

General	
Product Family	PCB Headers
Series	43915
Application	Power, Wire-to-Board
Comments	High Temperature Solder Type
Product Name	Mini-Fit Sr.™
Physical	
Breakaway	No
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Pitch - Mating Interface	10.00mm (.394")
Plating min - Termination	2.540µm (100µ")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	50A
Voltage - Maximum	600V

Solder Process Data	
Lead-free Process Capability	Wave Capable (TH only)

Material Info

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

43915Series

Mates With

43914 Mini-Fit Sr.™ Receptacle Housing