

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 130153-0017
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway® In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, Flying Lead Primary, TriTap Secondary (receptacle), 15A, 120V, 0.61m Cord Length

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Power Distribution
Series	<u>130153</u>
Enclosure Rating	NEMA 4X
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<u>Ground Fault Circuit Interrupter (GFCI) Products</u>
Product Name	Super-Safeway™
Receptacle Type	Triple
Type	GFCI Industrial Duty, Single Phase
UPC	78678801730
Woodhead	Yes

Physical	
Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Net Weight	999.990/kg
Number of Receptacles	3
Packaging Type	Carton

Electrical	
Cord Type	12/3 SJEOOW
Current - Maximum per Contact	15A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	240V

Material Info	
Old Part Number	09484



EU RoHS ELV and RoHS Compliant REACH SVHC Not Reviewed Low-Halogen Status Not Reviewed	China RoHS
---	-----------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
130153Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION