

- Rating: 3A/125VAC
- Contact resistance: 1A/2.5VDC 20mΩ or less
- Insulation resistance: 500VDC 100MΩ or more
- Dielectric Strength: 1000VAC 1 min.
- Electrical life: 10,000 cycles

- Circuit: 2P (SPST)
- Mounting hole: $\varnothing.701\pm.003"$
- Acceptable panel thickness: .028~.100"
- Mechanical life: 30,000 cycles

- Color: 10PA005 - red, 107-DS412W - white
- Net weight: gram/piece: 4.2g
- Contact: Copper
- Contact plate: Silver

Mountain Switch