


Headers

- Operating Temperature: -40°C to +105°C
- Processing Temperature: 230°C Max. for 60 seconds;
(260°C Max. for 10 seconds)
- UL Flammability Rating: 94V-0
- Contact Resistance: 20 milli Ohms Max.
- Current Rating: 1 Amp
- Dielectric Withstanding: 500 VAC
- Insulation Resistance: 5000 Megohms



SFH31 - N P P B - D 10 - SP - BK

$$B = .050'' [1.27 \text{ mm}]$$

Dimensions in [] are in millimeters, all others are in inches.

