


Features

- 500mW Power Dissipation
- High Stability
- Surface Mount Equivalents Available
- Hermetic Package
- V_Z - Tolerance $\pm 5\%$
- Lead Free Finish, RoHS Compliant (Note 2)

Mechanical Data

- Case: DO-35
- Case Material: Glass
- Moisture Sensitivity: Level 1 per J-STD-020
- Leads: Solderable per MIL-STD-202, Method 208
- Terminals: Finish - Sn96.5Ag3.5. Solderable per MIL-STD-202, Method 208
- Polarity: Cathode Band
- Marking: Type Number
- Weight: 0.13 grams (approximate)



DO-35		
Dim	Min	Max
A	25.40	—
B	—	4.00
C	—	0.60
D	—	2.00
All Dimensions in mm		

Maximum Ratings and Electrical Characteristics @ $T_A = 25^\circ\text{C}$ unless otherwise specified

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 1)	P_D	500	mW
Thermal Resistance, Junction to Ambient Air (Note 1)	$R_{\theta JA}$	300	$^\circ\text{C/W}$
Forward Voltage @ $I_F = 200\text{mA}$	V_F	1.1	V
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to +200	$^\circ\text{C}$

- Notes:
1. Valid provided that leads are kept at $T_L \leq 75^\circ\text{C}$ with lead length = 9.5mm (3/8") from case; derate above 75°C .
 2. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied, see EU Directive 2002/95/EC Annex Notes.

Electrical Characteristics

@T_A = 25°C unless otherwise specified

Table 1

Type Number	Zener Voltage Range (Note 3)			Test Current	Maximum Zener Impedance		Maximum Reverse Current		Maximum Temperature Coefficient @ I _{ZT}
	V _Z @ I _{ZT}				Z _{ZT} @ I _{ZT}	Z _{ZK} @ I _{ZK} = 0.25mA	I _R	@V _R	
	Nom (V)	Min (V)	Max (V)	mA					
1N5221B	2.4	2.28	2.52	20	30	1200	100	1.0	-0.085
1N5222B	2.5	2.38	2.63	20	30	1250	100	1.0	-0.085
1N5223B	2.7	2.57	2.84	20	30	1300	75	1.0	-0.080
1N5224B	2.8	2.66	2.94	20	30	1400	75	1.0	-0.080
1N5225B	3.0	2.85	3.15	20	29	1600	50	1.0	-0.075
1N5226B	3.3	3.14	3.47	20	28	1600	25	1.0	-0.070
1N5227B	3.6	3.42	3.78	20	24	1700	15	1.0	-0.065
1N5228B	3.9	3.71	4.10	20	23	1900	10	1.0	-0.060
1N5229B	4.3	4.09	4.52	20	22	2000	5.0	1.0	+0.055
1N5230B	4.7	4.47	4.94	20	19	1900	5.0	2.0	+0.030
1N5231B	5.1	4.85	5.36	20	17	1600	5.0	2.0	+0.030
1N5232B	5.6	5.32	5.88	20	11	1600	5.0	3.0	+0.038
1N5233B	6.0	5.70	6.30	20	7.0	1600	5.0	3.5	+0.038
1N5234B	6.2	5.89	6.51	20	7.0	1000	5.0	4.0	+0.045
1N5235B	6.8	6.46	7.14	20	5.0	750	3.0	5.0	+0.050
1N5236B	7.5	7.13	7.88	20	6.0	500	3.0	6.0	+0.058
1N5237B	8.2	7.79	8.61	20	8.0	500	3.0	6.5	+0.062
1N5238B	8.7	8.27	9.14	20	8.0	600	3.0	6.5	+0.065
1N5239B	9.1	8.65	9.56	20	10	600	3.0	7.0	+0.068
1N5240B	10	9.50	10.50	20	17	600	3.0	8.0	+0.075
1N5241B	11	10.45	11.55	20	22	600	2.0	8.4	+0.076
1N5242B	12	11.40	12.60	20	30	600	1.0	9.1	+0.077
1N5243B	13	12.35	13.65	9.5	13	600	0.5	9.9	+0.079
1N5244B	14	13.30	14.70	9.0	15	600	0.1	10	+0.082
1N5245B	15	14.25	15.75	8.5	16	600	0.1	11	+0.082
1N5246B	16	15.20	16.80	7.8	17	600	0.1	12	+0.083
1N5247B	17	16.15	17.85	7.4	19	600	0.1	13	+0.084
1N5248B	18	17.10	18.90	7.0	21	600	0.1	14	+0.085
1N5249B	19	18.05	19.95	6.6	23	600	0.1	14	+0.086
1N5250B	20	19.00	21.00	6.2	25	600	0.1	15	+0.086
1N5251B	22	20.90	23.10	5.6	29	600	0.1	17	+0.087
1N5252B	24	22.80	25.20	5.2	33	600	0.1	18	+0.087
1N5253B	25	23.75	26.25	5.0	35	600	0.1	19	+0.089
1N5254B	27	25.65	28.35	4.6	41	600	0.1	21	+0.090
1N5255B	28	26.60	29.40	4.5	44	600	0.1	21	+0.091
1N5256B	30	28.50	31.50	4.2	49	600	0.1	23	+0.091
1N5257B	33	31.35	34.65	3.8	58	700	0.1	25	+0.092
1N5258B	36	34.20	37.80	3.4	70	700	0.1	27	+0.093
1N5259B	39	37.05	40.95	3.2	80	800	0.1	30	+0.094
1N5260B	43	40.85	45.15	3.0	93	900	0.1	33	+0.095
1N5261B	47	44.65	49.35	2.7	105	1000	0.1	36	+0.095
1N5262B	51	48.45	53.55	2.5	125	1100	0.1	39	+0.096
1N5263B	56	53.20	58.80	2.2	150	1300	0.1	43	+0.096
1N5264B	60	57.00	63.00	2.1	170	1400	0.1	46	+0.097
1N5265B	62	58.90	65.10	2.0	185	1400	0.1	47	+0.097
1N5266B	68	64.60	71.40	1.8	230	1600	0.1	52	+0.097
1N5267B	75	71.25	78.75	1.7	270	1700	0.1	56	+0.098

Notes: 3. Based on dc measurement at thermal equilibrium; lead length = 9.5mm (3/8"); thermal resistance of heat sink = 30°C/W.



**NOT RECOMMENDED FOR
NEW DESIGN, USE
MMSZ52xxB**

Ordering Information (Notes 4 & 5)

Device	Packaging	Shipping
(Type Number)-A	DO-35	5K/Ammo Pack
(Type Number)-T	DO-35	10K/Tape & Reel

Notes: 4. Add "-A" or "-T" to the appropriate type number in Table 1. Example: 6.2V Zener = 1N5234B-A for ammo pack.
5. For packaging details, visit our website at <http://www.diodes.com/datasheets/ap02008.pdf>.

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2011, Diodes Incorporated

www.diodes.com