

## FEATURES

### OMT25- Series

- Two mounting methods: flange or panel mount
- Three different tones and combinations available
- Small size with rich sound output

### OMT200-, OMT260-, OMT35- Series

- Flange mounting with two lead wires
- Small size and lightweight
- Rich sound output and low current drain



### ALL

- Operating temperature -20°C~60°C; Storage temperature -30°C~70°C

**This product has been  
DISCONTINUED**

# Piezo Audio Indicators

## Flange Mounting/Panel Mounting Types



| Model No. | Oscillating frequency (Hz ±500) | Operating voltage | Sound pressure @30cm/12vdc (dB min.) | Current consumption (mA max.) | Tone*         | Weight (g) |
|-----------|---------------------------------|-------------------|--------------------------------------|-------------------------------|---------------|------------|
| ✓ OMT200  | 3100                            | 3-20 DC           | 78                                   | 12 <sup>†</sup>               | Continuous    | 4.5        |
| ⊕ OMT200L | 3100                            | 3-20 DC           | 93                                   | 5 <sup>†</sup>                | Continuous    | 4.5        |
| ⊕ OMT250  | 3500                            | 4-28 DC           | 87                                   | 8                             | Continuous    | 10.2       |
| ⊕ OMT251  | 3500                            | 4-28 DC           | 85                                   | 5                             | Fast pulse    | 10.2       |
| ✓ OMT253  | 3500                            | 4-28 DC           | 87                                   | 6                             | Slow pulse    | 10.2       |
| ✓ OMT255  | 3500                            | 4-28 DC           | 90                                   | 8                             | Cont. & F. P. | 10.2       |
| ✓ OMT257  | 3500                            | 4-28 DC           | 90                                   | 8                             | Cont. & S. P. | 10.2       |
| ✓ OMT260  | 3500                            | 3-28 DC           | 88                                   | 5 <sup>†</sup>                | Continuous    | 15         |
| ✓ OMT260L | 3500                            | 3-20 DC           | 93                                   | 8 <sup>†</sup>                | Continuous    | 15         |
| ⊕ OMT350  | 2800                            | 3-28 DC           | 85                                   | 8                             | Continuous    | 14.6       |
| ✓ OMT350L | 2800                            | 3-20 DC           | 92                                   | 12                            | Continuous    | 14.6       |
| ✓ OMT351  | 2800                            | 3-28 DC           | 81                                   | 6                             | Pulse         | 14.6       |
| ✓ OMT351L | 2800                            | 3-20 DC           | 88                                   | 8                             | Pulse         | 14.6       |

⊕ = Most popular stock values

✓ = Stock values

⊕ = Non-stock values subject to minimum handling charge per item

\* Pulse rate at 12VDC: Fast, 3.0 Hz ±20%; Slow, 1.2 Hz ±20% <sup>†</sup> at 12 VDC