



- High protection rating IP 65
- B 15 d socket integrated in the base
- Safe CAGE CLAMP® technology
- Small shape with high dome
- Optimum illumination
- Available for base or bracket mounting
- Connection without the need to disassemble the product

Housing: PA 6.6 GF, black
Dome: Polycarbonate, transparent
Connection: CAGE CLAMP® technology up to 2,5mm² max.
Contact protection according to VDE

210

Fixing:

**Base mounting
with flat seal**

213

Bracket mounting,
including cable gland
M 12 x 1,5
57 mm x 82 mm
61 g
max. 250 V
B 15 d, 10 Watt max.
via removal of dome

Dimensions(Diameter x Height):57 mm x 82 mm

Weight:

55 q

Operating voltage:

max. 250 V

Bulb socket:

B 15d. 10 Watt max.

Bulb change:

via removal of dome

Bulbs not included in assembly

B 15d, 10 Watt max.

via removal of dome

210 Permanent/LED/Flashing Beacon

