




Dimensions: mm (in.)



Mouser Stock No.	No. of Pos.	Dim A. mm (in.)	Dim B. mm (in.)	Actuator
106-EM02-EV	2	4.98 (.196)	2.54 (.10)	Raised
106-EM03-EV	3	7.52 (.296)	5.08 (.20)	Raised
106-EM04-EV	4	10.06 (.396)	7.62 (.30)	Raised
106-EM06-EV	6	15.14 (.596)	12.70 (.50)	Raised
106-EM08-EV	8	20.22 (.796)	17.78 (.70)	Raised
106-EM10-EV	10	25.3 (.996)	22.86 (.90)	Raised
106-EMR2T-EV	2	4.98 (.196)	2.54 (.10)	Recessed
106-EMR3T-EV	3	7.52 (.296)	5.08 (.20)	Recessed
106-EMR4T-EV	4	10.06 (.396)	7.62 (.30)	Recessed
106-EMR6T-EV	6	15.14 (.596)	12.70 (.50)	Recessed
106-EMR8T-EV	8	20.22 (.796)	17.78 (.70)	Recessed
106-EMR10T-EV	10	25.3 (.996)	22.86 (.90)	Recessed

Electrical Specifications:

- Rating: Non-switching: 100mA/50V DC; Switching: 25mA/24V DC
- Contact resistance: 100mΩ max. (initial)
- Insulation resistance: 100MΩ min.

Mechanical Specifications:

- Operating temperature: -20°C ~ +85°C
- Operation force: 1000gf max.

Soldering Process:

- Reflow Temperature: 260°maximum (not washable)

Note:

- RoHS Compliant

DIP Switches (SMD)

106-EM02-EV, 106-EM03-EV, 106-EM04-EV, 106-EM06-EV, 106-EM08-EV,
106-EM10-EV, 106-EMR2T-EV, 106-EMR3T-EV, 106-EMR4T-EV,
106-EMR6T-EV, 106-EMR8T-EV, 106-EMR10T-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[106-EM06-EV](#) [106-EMR3T-EV](#) [106-EMR4T-EV](#) [106-EM08-EV](#) [106-EM03-EV](#) [106-EMR8T-EV](#) [106-EMR2T-EV](#)
[106-EM04-EV](#) [106-EMR6T-EV](#) [106-EM02-EV](#) [106-EM10-EV](#) [106-EMR10T-EV](#)