



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT MATERIAL: GOLD FLASH over Silver Plate
OVER COPPER ALLOY
6. OPERATING FORCE: 425 ± 100 CM/STANDARD
7. OPERATING TEMP: -30° to 85° C
8. CIRCUIT DP: 12 POSITIONS, 30° INDEX.
9. DIELECTRIC STRENGTH: 1000V RMS min.@Sea Level
10. DESIGNATE MAJOR DIMENSIONS
11. HARDWARE SUPPLIED ON SWITCH - SEE BELOW



STOPRING, LOCKWASHER, & HEXNUT



CONTACT CONFIGURATION
Timing: Non Shorting (BBW)



TERMINATION DETAIL
SCALE 2X



E-SWITCH®			
TITLE			
KC-52-A (9.5mm)-01-N-L-F			
SCALE			
1.5:1			
DATE			
4/16/02			
DR			
CJB			
DWG			
G510241			
REV			
C			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
REV.	ECN No.	DESCRIPTION	DATE
A	12072	RELEASED FOR PRODUCTION	4/16/02
B	12238	REV PART DESC. PER CATALDG	6/13/02
C	12831	REVISED NOTE 11	3/3/03