








DG103-5.0
DG103-5.08



APPROVAL Electrical

Standard

Rated voltage

Rated current

Wire range

Withstanding voltage



UL

300V

10A

24-12AWG

AC2000V/1Min

IEC

250V

24A

2.5mm²

Menchanical

Torque

Ambient temperature

Strip length

Dimensions

pitch

Poles

0.4Nm(3.5Lb-In)

-40℃~+105℃

7mm

5.0mm(.197") 5.08mm(.200")

2P,3P-24P

Material

Housing

Screws

Pin header

Cage

PA66,UL94V-0

M2.5,Steel, Cr³⁺ Znplated

Brass,Tin plated

Brass,Ni plated

HOW TO ORDER :

- **P** - **1** -

X	X	X
Customer Request		


Series number

No.of pole

1	Single pitch
2	Double pitch

Color

1 Grey	4 Green	7 Trans Parent
2 Blue	5 Orange	8 Yellow
3 Black	6 Red	9 White



DEGSON ELECTRONICS CO., LTD.

NAME

DG103-5.0

DG103-5.08