

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [82-24-8519](#)
Status: **Active**
Description: 2.50mm Pitch Round Conductor Flat Cable - 24 AWG (7 x 32) Stranded, Topcoat, 19 Circuits, Reel 30.48m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR61126
UL	E61522

General

Product Family	Cable
Series	24492
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800754980494

Physical

Cable Length	30.48m
Circuits (Loaded)	19
Insulation	PVC
Packaging Type	Reel
Pitch - Termination Interface	2.50mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	24
Wire/Cable Type	(7x32) Stranded, Topcoat

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	300V

Material Info

Old Part Number	24492-19-100B
-----------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-24492-001
---------------	--------------




image - Reference only **Series**

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[24492Series](#)

Use With
[42219](#) SPOX™ IDT Receptacle