




LOC	DIST	REVISIONS					
AJ	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K1	REV PER ECO 06-029805	2/6/2007	DW	JL

1. USE WITH COMMERCIAL HAND TOOL: 220190-1
2. MAXIMUM PANEL THICKNESS: 6.10 [.240]
3. SEE I.S. 9051
4. SEE SEPERATE RESTRICTED CUSTOMER DRAWING WITH THIS PART NUMBER
5. CONSISTS OF (8) UNASSEMBLED CONNECTORS




RECOMMENDED PANEL CUTOUT
SCALE: 3:1



RECOMMENDED STRIP LENGTH
SCALE: 3:1

	OBSOLETE	RG-58/U, 58A/U, 58B/U, 58C/U, 141/U, 141A/U	34.93 [1.375]	220189-1	220187-1	—	9-50427-1	329633	1-329632-2	1-329631-2	221149-6	227461-2	9-228980-0
	4	—	—	—	—	—	—	—	—	—	—	—	1-228980-7
SUPERSEDED BY 413771-6		BELDEN 89907	40.46 [1.593]	220189-1	220187-1	—	9-228783-0	329633	1-329632-2	1-329631-2	2-221149-6	227461-2	1-228980-6
	OBSOLETE	BELDEN 9907	34.93 [1.375]	220189-1	220187-1	—	9-50427-1	329633	1-329632-2	1-329631-2	2-221149-6	227461-2	1-228980-5
SUPERSEDED BY 1-228980-6	5	BELDEN 9907	34.93 [1.375]	220189-1	220187-1	—	9-50427-1	329633	1-329632-2	1-329631-2	2-221149-6	227461-2	1-228980-3
	OBSOLETE	BELDEN 8281	40.64 [1.600]	220189-6	—	—	9-331256-0	329633	1-329632-2	1-329631-2	221149-6	227461-4	228980-8
		RG-174/U, 188/U, 316/U	34.93 [1.375]	220210-1	220009-5	21427-4	9-328666-0	329633	1-329632-2	1-329631-2	2-221149-0	227461-1	228980-7
		RG-59/U, 59A/U, 59B/U, 62/U, 62A/U, 62B/U	34.93 [1.375]	220189-2	220187-2	—	9-50428-0	329633	1-329632-2	1-329631-2	1-221149-3	227461-3	228980-6
		RG-58/U, 58A/U, 58B/U, 58C/U, 141/U, 141A/U	34.93 [1.375]	220189-1	220187-1	—	9-50427-1	329633	1-329632-2	1-329631-2	221149-6	227461-2	228980-5
		FOR USE WITH CABLE	L	DIE SET 	CRIMP TOOLING	 BUSHING QTY=1	 FERRULE QTY=1	 GASKET QTY=1	 LOCKWASHER QTY=1	 JAM NUT QTY=1	 CONTACT QTY=1	 JACK ASSEMBLY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN M. E. COWHER	3-8-91	 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK J. T. LIPPETT	3-12-91		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPRO M. PHILLIPS	3-12-91	NAME JACK, BHD, COMMERCIAL, BNC	
	0 PLC ± -	PRODUCT SPEC			
	1 PLC ± -	108-12047			
	2 PLC ± 0.41 [016]	APPLICATION SPEC			
	3 PLC ± -	—		SIZE CAGE CODE DRAWING NO. RESTRICTED TO	
	4 PLC ± -	—			A1 00779 C-228980
	ANGLES ± -	—			
MATERIAL	FINISH	WEIGHT		SCALE 10:1 SHEET 1 OF 1 REV K1	
—		—		CUSTOMER DRAWING	