






PRODUCT NUMBER
SEE TABLE



mat'l. code				surface	tolerance	projection	product family
NOTE 3				ISO 406	ISO 1101		HPC
ltr	ecn no	dr	date	tolerances unless otherwise specified			
J	v00254	JWS	1/13/00	angles	.XX±.01/XX±0.3	INCH/MM	title 3 ROW R/A RECEPTACLE SOLDER TO BOARD, 0 G.P.
K	v01300	HTB	4/13/00	linear	.XXX±.006/XX±0.13		
L	v05-0895	DCH	9/20/05	0'±2'	.XXX±.0020/XXX±0.06		
M	v05-1052	DAI	11/17/05	dr	G.PETERS	6/5/96	dwg no
N	M06-0283	MHT	7/27/06	engr	S.CLARK	6/3/95	sheet 1 of 5 size
P	M07-0099	AGS	2/09/07	chr	S.CLARK	6/5/95	A3
R	M08-0280	AGS	9/30/08	appd	S.CLARK	6/5/95	type
revision	R	R	R	R	R	R	Product Customer Drawing
sheet index	sheet	1	2	3	4	5	

PRODUCT NUMBER



SEE TABLE



SECTION U-U

SPECIAL FEATURE OPTION "A"



SEE NOTE 6



SECTION U-U



SPECIAL FEATURE OPTION "B"

SEE NOTE 6



SECTION U-U



SELF TAPPING SCREW, 2X



SEE NOTE 7



SPECIAL FEATURE OPTION "C"

SEE NOTE 6



SECTION U-U

SELF TAPPING SCREW, 2X



SPECIAL FEATURE OPTION "D"

SEE NOTE 6

mat'l. code NOTE 3				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified		 INCH/MM	HPC
R				angles	linear		title
							3 ROW R/A RECEPTACLE
							SOLDER TO BOARD, 0 G.P.
						scale 1:1	dwg no
				dr	G.PETERS	6/5/96	sheet 3 of 5 size
				engr	S.CLARK	6/3/95	50294
				chr	S.CLARK	6/5/95	A3
				appd	S.CLARK	6/5/95	type
sheet	revision						Product Customer Drawing
index	sheet						

FCI
FCIconnect.com

Copyright FCI

form A3

PRODUCT NUMBER NOTE 1 AND 2	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH ±.010/0.25	SPECIAL FEATURES SEE NOTE 6	TAIL PLATING	CONTACT PLATING SEE NOTE 10
50294-1YYYY	YYY	.125/3.18	NONE	TIN-LEAD	30μ"/0.76μ Au
50294-1YYEYA	YYY	.125/3.18	"A"		30μ"/0.76μ Au
50294-1YYEYB	YYY	.125/3.18	"B"		30μ"/0.76μ Au
50294-1YYEYC	YYY	.125/3.18	"C"		30μ"/0.76μ Au
50294-1YYEYD	YYY	.125/3.18	"D"		30μ"/0.76μ Au
50294-1YYFY	YYY	.145/3.68	NONE		30μ"/0.76μ Au
50294-1YYFYB	YYY	.145/3.68	"B"		30μ"/0.76μ Au
50294-1YYFYC	YYY	.145/3.68	"C"		30μ"/0.76μ Au
50294-1YYFYD	YYY	.145/3.68	"D"		30μ"/0.76μ Au
50294-1YYHY	YYY	.180/4.57	NONE		30μ"/0.76μ Au
50294-1YYHYB	YYY	.180/4.57	"B"		30μ"/0.76μ Au
50294-1YYHYC	YYY	.180/4.57	"C"		30μ"/0.76μ Au
50294-1YYHYD	YYY	.180/4.57	"D"		30μ"/0.76μ Au
50294-3YYEY	YYY	.125/3.18	NONE		50μ"/1.27μ Au
50294-3YYEYA	YYY	.125/3.18	"A"		50μ"/1.27μ Au
50294-3YYEYB	YYY	.125/3.18	"B"		50μ"/1.27μ Au
50294-3YYEYC	YYY	.125/3.18	"C"		50μ"/1.27μ Au
50294-3YYEYD	YYY	.125/3.18	"D"		50μ"/1.27μ Au
50294-3YYFY	YYY	.145/3.68	NONE		50μ"/1.27μ Au
50294-3YYFYB	YYY	.145/3.68	"B"		50μ"/1.27μ Au
50294-3YYFYC	YYY	.145/3.68	"C"		50μ"/1.27μ Au
50294-3YYFYD	YYY	.145/3.68	"D"		50μ"/1.27μ Au
50294-3YYHY	YYY	.180/4.57	NONE		50μ"/1.27μ Au
50294-3YYHYB	YYY	.180/4.57	"B"		50μ"/1.27μ Au
50294-3YYHYC	YYY	.180/4.57	"C"		50μ"/1.27μ Au
50294-3YYHYD	YYY	.180/4.57	"D"	TIN-LEAD	50μ"/1.27μ Au

PRODUCT NUMBER NOTE 1 AND 2	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH ±.010/0.25	SPECIAL FEATURES SEE NOTE 6	TAIL PLATING	CONTACT PLATING SEE NOTE 10
50294-1YYYYELF	YYY	.125/3.18	NONE	TIN	30μ"/0.76μ Au
50294-1YYYYEALF	YYY	.125/3.18	"A"		30μ"/0.76μ Au
50294-1YYYYEBLF	YYY	.125/3.18	"B"		30μ"/0.76μ Au
50294-1YYYYECLF	YYY	.125/3.18	"C"		30μ"/0.76μ Au
50294-1YYYYEDLF	YYY	.125/3.18	"D"		30μ"/0.76μ Au
50294-1YYYYFLF	YYY	.145/3.68	NONE		30μ"/0.76μ Au
50294-1YYYYFBLF	YYY	.145/3.68	"B"		30μ"/0.76μ Au
50294-1YYYYFCLF	YYY	.145/3.68	"C"		30μ"/0.76μ Au
50294-1YYYYFDLF	YYY	.145/3.68	"D"		30μ"/0.76μ Au
50294-1YYYYHLF	YYY	.180/4.57	NONE		30μ"/0.76μ Au
50294-1YYYYHBLF	YYY	.180/4.57	"B"		30μ"/0.76μ Au
50294-1YYYYHCLF	YYY	.180/4.57	"C"		30μ"/0.76μ Au
50294-1YYYYHDLF	YYY	.180/4.57	"D"		30μ"/0.76μ Au
50294-3YYYYELF	YYY	.125/3.18	NONE		50μ"/1.27μ Au
50294-3YYYYEALF	YYY	.125/3.18	"A"		50μ"/1.27μ Au
50294-3YYYYEBLF	YYY	.125/3.18	"B"		50μ"/1.27μ Au
50294-3YYYYECLF	YYY	.125/3.18	"C"		50μ"/1.27μ Au
50294-3YYYYEDLF	YYY	.125/3.18	"D"		50μ"/1.27μ Au
50294-3YYYYFLF	YYY	.145/3.68	NONE		50μ"/1.27μ Au
50294-3YYYYFBLF	YYY	.145/3.68	"B"		50μ"/1.27μ Au
50294-3YYYYFCLF	YYY	.145/3.68	"C"		50μ"/1.27μ Au
50294-3YYYYFDLF	YYY	.145/3.68	"D"		50μ"/1.27μ Au
50294-3YYYYHLF	YYY	.180/4.57	NONE		50μ"/1.27μ Au
50294-3YYYYHBLF	YYY	.180/4.57	"B"		50μ"/1.27μ Au
50294-3YYYYHCLF	YYY	.180/4.57	"C"		50μ"/1.27μ Au
50294-3YYYYHDLF	YYY	.180/4.57	"D"	TIN	50μ"/1.27μ Au

TABLE CONTINUED ON SHEET 5

mat'l. code NOTE 3				surface ISO 1302	tolerance ISO 406 ISO 1101	projection FIRST ANGLE	product family HPC	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
R				angles	linear	XX±.01/XX±0.3 XXX±.005/XXX±0.13 XXXX±.0020/XXXX±0.05	3 ROW R/A RECEPTACLE SOLDER TO BOARD, 0 G.P.	
				0'±2'			scale 1:1	
				dr	G.PETERS	6/5/96	dwg no	sheet 4 of 5 size
				engr	S.CLARK	6/3/95	50294	A3
				chr	S.CLARK	6/5/95		
				appd	S.CLARK	6/5/95		
sheet	revision			type Product Customer Drawing				
index	sheet							



FCIconnect.com

Copyright FCI

PRODUCT NUMBER NOTE 1 AND 2	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH ±.010/0.25	SPECIAL FEATURES SEE NOTE 6	TAIL PLATING	CONTACT PLATING SEE NOTE 10
50294-5YYYE	YYY	.125/3.18	NONE	TIN/LEAD	30μ"/0.76μ GXT
50294-5YYYELF	YYY	.125/3.18	NONE	TIN	
50294-5YYYEA	YYY	.125/3.18	"A"	TIN/LEAD	
50294-5YYYEALF	YYY	.125/3.18	"A"	TIN	
50294-5YYYEB	YYY	.125/3.18	"B"	TIN/LEAD	
50294-5YYYEBLF	YYY	.125/3.18	"B"	TIN	
50294-5YYYEC	YYY	.125/3.18	"C"	TIN/LEAD	
50294-5YYYECLF	YYY	.125/3.18	"C"	TIN	
50294-5YYYED	YYY	.125/3.18	"D"	TIN/LEAD	
50294-5YYYEDLF	YYY	.125/3.18	"D"	TIN	
50294-5YYYF	YYY	.145/3.68	NONE	TIN/LEAD	
50294-5YYYFLF	YYY	.145/3.68	NONE	TIN	
50294-5YYYFB	YYY	.145/3.68	"B"	TIN/LEAD	
50294-5YYYFBLF	YYY	.145/3.68	"B"	TIN	
50294-5YYYFC	YYY	.145/3.68	"C"	TIN/LEAD	
50294-5YYYFCLF	YYY	.145/3.68	"C"	TIN	
50294-5YYYFD	YYY	.145/3.68	"D"	TIN/LEAD	
50294-5YYYFDLF	YYY	.145/3.68	"D"	TIN	
50294-5YYYH	YYY	.180/4.57	NONE	TIN/LEAD	
50294-5YYYHLF	YYY	.180/4.57	NONE	TIN	
50294-5YYYHB	YYY	.180/4.57	"B"	TIN/LEAD	
50294-5YYYHBLF	YYY	.180/4.57	"B"	TIN	
50294-5YYYHC	YYY	.180/4.57	"C"	TIN/LEAD	
50294-5YYYHCLF	YYY	.180/4.57	"C"	TIN	
50294-5YYYHD	YYY	.180/4.57	"D"	TIN/LEAD	
50294-5YYYHDLF	YYY	.180/4.57	"D"	TIN	30μ"/0.76μ GXT

mat'l. code				surface ISO 1902		tolerance ISO 406 ISO 1101		projection		product family	
NOTE 3										HPC	
ltr	ecn no	dr	date	tolerances unless otherwise specified							
R				angles	linear	.XX±.01/XX±0.3 .XXX±.006/XX±0.13				title	
				0'±2'		.XXX±.0020/XXX±0.06		scale 1:1		3 ROW R/A RECEPTACLE SOLDER TO BOARD, 0 G.P.	
				dr	G.PETERS	6/5/96				dwg no	
				engr	S.CLARK	6/3/95				sheet 5 of 5 size	
				chr	S.CLARK	6/5/95				50294 A3	
				appd	S.CLARK	6/5/95				type Product Customer Drawing	
sheet	revision										
index	sheet										

form A3