


MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING
924CE31-Y3L1



REPLACES

RELEASE NO. CO-69061

924CE31-Y3L1

M



DRAWING
NUMBER

ISSUE
1


CHECK

REVISIONS

CHECK



Ø .48 X .20 WIDE
HARDENED STEEL
ROLLER




NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - THE MINIMUM PLUNGER TRAVEL PAST BREAK, FOR A SAFE CONTACT GAP IS .060
- 3 - LUBRICANT AND SEALS RATED TO -40° C

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 5.8 LB MAX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N C D B

5A 1/10 HP - 125 OR 250 VAC



SCALE FULL

DO NOT
SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT

DDM/CAD

DRAWN

S A V 10 OCT 91