



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		B	REV PER EC 0S12-0302-05	14DEC05	BC	GS



- 1

SUITABLE FOR FEMALE TYPE M CONNECTORS.
- 2

CONTACT SPRING: BERYLLIUM COPPER.
CONTACT BODY: BRASS.
RETAINING RING: BERYLLIUM COPPER.
- 3

CONTACT FINISH: 0.00127[.000050] MIN GOLD IN CONTACT AREA,
0.00254[.000100] MIN TIN IN AREA "X", ALL OVER
0.00127[.000050] NICKEL.
- 4

CONTACT FINISH: 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00254[.000100] MIN TIN IN AREA "X", ALL OVER
0.00127[.000050] NICKEL.

OBSOLETE	4	5148513-2
	3	5148513-1
	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.CARBO	15JUL05	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK A.SHARPE	15JUL05						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.SHARPE	15JUL05	NAME POWER CONTACT, EUROCARD TYPE M, FEMALE 90 DEGREE, PRINTED CIRCUIT BOARD MOUNT			
		0 PLC ± -		PRODUCT SPEC		—			
		1 PLC ± -		—					
		2 PLC ± -		APPLICATION SPEC		—			
		3 PLC ± -		—					
		4 PLC ± -		—		—			
		ANGLES ± -		—					
MATERIAL 		FINISH SEE TABLE		WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C-5148513	RESTRICTED TO —
CUSTOMER DRAWING						SCALE 8:1	SHEET 1 of 1	REV B	