

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DF

S0

P

LTR

DESCRIPTION

DATE

DWN

APVD


G

REV & REDRAWN; 0600-6006-96

12-96

CT

SG

 ϕ .62
[15.7] ϕ .06 [1.5]
PIN TYP.50
[12.7]1.87
[47.5].87
[22.1] ϕ .50
[12.7].88 [22.4]
BARREL DEPTH
TYP.38 [9.6]
MIN FULL THD
TYP1/2-20 UNF
TYP

1. RECEPTACLE TO MATE WITH AMP LGH-1
LEAD ASSY WITH .88 [22.4] BARREL DEPTH.

OBSOLETE

GOLD PLATED PIN

830149-2

-

TIN PLATED PIN

830149-1

REMARKS

DESCRIPTION

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.C. THOMAS 12-9-96CHK
S. GLATFELTER 1-15-97APVD
S. GLATFELTER 1-15-97

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMPAMP Incorporated
Harrisburg, PA 17105-3608NAME
RCPT ASSY, FEED-THRU FOR
SPLICE APPLICATIONS, LGH-1

SIZE


CAGE CODE

DRAWING NO

A3

00779

C-830149

SCALE
2:1SHEET
1 OF 1REV
GDIMENSIONS:
INCHES [mm]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±
1 PLC ±
2 PLC ±.02 [0.5]
3 PLC ±
4 PLC ±
ANGLES ±
COLOR

BLACK

MATERIAL

MOLDED GLASS EPOXY