


Heavy Duty pH/ORP/Temp Kit



Features:

- Dual display for pH or mV and Temperature (°C/°F)
- Large 1.4" (36mm) LCD display
- Easy 2 point Cal (pH 7) and Slope (pH 4 or pH 10) adjustments
- Manual and Auto Temperature Compensation using temperature probe
- Low Battery Indicator
- Min/Max/Avg, Auto off and Data Hold
- Built-in RS-232 PC interface with optional 407001 Data Acquisition Software and 380340 Datalogger
- Includes meter, mini pH electrode (60120B) with 39" (1m) cable, temperature probe (850188), protective holster with stand, and case.
- Optional AC adaptor



Specifications	Range
pH	0.00 to 14.00pH
mV	0 to 1999mV
Temperature	32 to 149°F (0 to 65°C)
Max Resolution	0.01pH, 1mV, 0.1°
Basic Accuracy	±0.03pH, ±0.5%mV, ±1.8°F/1°C
PC Interface	Optional 407001 software
Memory	Optional 380340 datalogger
Dimensions	7 x 2.9 x 1.3" (178 x 74 x 33mm)
Weight	13oz (388g)

Ordering Information:

407228-KitHeavy Duty pH/ORP/Temp Kit
407228-NIST ...Heavy Duty pH/ORP/Temp Kit with NIST Certificate



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[407228](#)