


Lamp Specification

Wamco Part No.	Envelope Size	Base Type	Rating
WL-A1H	T1 $\frac{3}{4}$	MF	115V AC

Test Volts	Current (mA)			Light Output Color / Appearance	Life Hours
	Min.	Nom.	Max.		
115V AC	---	1.20	---	High Brightness Red	25,000 Hrs

Dimensional Characteristics:

1. Base = Nickel-Plated Brass Construction.
2. Recommended Series Resistor 47K Ω $\frac{1}{4}$ W for 100~125V operation.
3. Dark effect reduced.
4. Caution: Bulb may shatter and/or circuit may be damaged without external series resistance.



Title

**T1 $\frac{3}{4}$ Midget Flange Base
115V AC Red Neon Lamp**

Drawn	05/27/09	TI	Notes Unless otherwise specified, all dimensions are in inches.	Rev 1
Checked	05/27/09	EB		
Approved	05/28/09	EB		