


LEDs & INDICATORS


509 M-LED Series

- Threaded body for panel thicknesses 0.5-2.5mm, panel cut-out 6.5mm diameter
- 3.2mm LED with pin termination, anode pin cut short
- Polycarbonate lens with 65° viewing angle
- Nickel plated brass body, supplied with nut and shakeproof washer
- Red, green and amber lenses colour options as standard
- Blue and clear lenses to order
- Maximum working temperature 80°C




TYPE NO.	509	X	13	-	LED	-	T	/	XXX
509 Series Indicator	509								
Lens cylinder flat	1								
Lens cylinder domed	2								
Pin termination	13								
LED, anode pin cut short	LED								
Transparent lens	T								
Lens colour Red	RED								
Lens colour Green	GRN								
Lens colour Amber	AMB								
Lens colour Blue	BLU								
Lens colour Clear	CLR								

Body Dimensions



514 23-LED Series

- Press-fit body for various panel thickness, panel cut-out 8.0mm diameter
- LED pin termination, anode pin cut short
- Polycarbonate body/bezel and lens
- Red, green, amber, and blue lens colour options as standard
- Maximum working temperature 105°C



TYPE NO.	514	1	13	-	LED	-	T	/	XXX
515 Series Indicator	514								
Lens Type	1								
Pin termination	13								
LED, anode pin cut short	LED								
Transparent lens	T								
Lens colour Red	RED								
Lens colour Green	GRN								
Lens colour Amber	AMB								
Lens colour Blue	BLU								

Body Dimensions

