



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	3/31/04	T CLARK
A1	CN RELEASE	11/19/07	D FRISIELLO
B	ECN3117: CHANGED FORMAT, UPDATED WIRING MAP, ADDED ROHS STAMP	12/14/07	D. PARHAM
C	ECN 3779: DEFINED COLOR TO LIGHT GRAY, NEW FORMAT	1/6/09	D FRISIELLO



WIRING MAP		
"P1"	WIRE COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK / WHITE	13
14	BROWN / WHITE	14
15	RED / WHITE	15
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CRMN15MF-2.5	2.5	.76
CRMN15MF-5.0	5.0	1.52
CRMN15MF-10.0	10.0	3.05
CRMN15MF-15.0	15.0	4.57

SUPPLIED WITH THUMBSCREWS IN PLACE
NOTE: SUPPLIED WITH OPTIONAL USE HARDWARE AND INSTRUCTIONS
CABLE INTERCONNECTION HARDWARE: (4) SCREWLOCKS, H= .191"
PANEL MOUNT HARDWARE: (4) SCREWLOCKS, H= .160"

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm) OVERALL CABLE LENGTH TOLERANCE: ≤12 (305) ±.1 (25) / -0 >12 (305) ≤60 (1524) ±.2 (51) / -0 >60 (1524) ≤120 (3048) ±.4 (102) / -0 >120 (3048) ≤300 (7620) ±.6 (152) / -0 >300 (7620) ±.8 (19) / -0 ALL OTHER DIMENSIONAL TOLERANCES: X = .3 XX = .15	APPROVALS DRAWN BY T CLARK CHECKED BY D PARHAM APPROVED BY C MCCORMICK 3/31/2004	DATE 3/10/2004 3/30/2004 3/31/2004
PROJECTION ⊕	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR CRMN-FS01	L-com Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
CATEGORY DATA CABLING	PRODUCT DESCRIPTION CABLE, DB15M/F REVERSIBLE HDWR	SIZE B
PSCM NO. 43321	DWG. NO. CRMN15MF	REV. C
SCALE: 1:1	CAD FILE: CRMN15MF.SLDRAW	SHEET 1 OF 1