




REVISIONS					
REV		DESCRIPTION	DATE	DWN	APVD
H6	REVISED	ECR-16-002841	18MAY2017	KF	TK





プリント基板取付穴寸法図
(MOUNTING DIMENSIONS FOR P.C.BOARD)

- 板厚, 1.6±0.15
(P.C.B. THICKNESS, 1.6±0.15)
- 公差, ±0.1
(TOLERANCE, ±0.1)



- 注記:
- △ 相手ハウジングと所定の機能を満たしてあみ合えること。
 - △ フードの戻りは0.2以内。
 - 3 プリント基板への取付けは JIS B1115 M3 1種のタッピンネジで締め付けた後はんだ付けする。
 - 4 適用製品規格: 108-5093
 - △ 全面ニッケルめっき上に金フラッシュ及び接触部のみ厚さ0.76μm以上の金めっき。
 - △ 全面ニッケルめっき上に金フラッシュ及び接触部のみ厚さ0.38μm以上の金めっき。
 - △ A 面より2mmの範囲で測定のこと。
 - 8 相手ハウジングとのかん合力は、29.4N以下
但し、リセグタルコンタクトは含まない。
 - △ TABは挿入されていない(3-171882-4のみ)
 - △ 金めっき位置番号: 下記参照のこと
 - 11 金めっき端子のみ、基板はんだ付部にはんだめっきを施す。

- NOTE:
- △ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
 - △ WARPAGE 0.2 MAX.
 - 3 SOLDERING AFTER MOUNTING P.C. BOARD BY 3mmDIA TAPPING SCREW, SPECIFIED IN JIS B1115
 - 4 PRODUCT SPEC NO. 108-5093
 - △ GOLD FLASH AND GOLD PLATING 0.76μm MIN. ONLY CONTACT AREA OVER NICKEL PLATING
 - △ GOLD FLASH AND GOLD PLATING 0.38μm MIN. ONLY CONTACT AREA OVER NICKEL PLATING
 - △ TO BE MEASURED WITHIN 2mm FROM A
 - 8 IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N MAX. WITHOUT RECEPTACLE CONTACT
 - △ TAB MUST NOT BE INSERTED (3-171882-4 ONLY)
 - △ GOLD PLATED POSITION NUMBER.
 - 11 TIN LEAD PLATING IN PART OF SOLDER TAIL SIDE ONLY GOLD PLATED CONTACT.



①～⑬	△	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	4-5171882-1
①～⑬	△	PRE-TIN	PRE-TIN	NATURAL	2-5171882-1
①～⑬	△	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-5171882-1
①～⑬	△	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	4-171882-1
①～⑬	△	PRE-TIN	PRE-TIN	NATURAL	4-171882-1
①～⑬	△	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	GREEN	2-171882-4
①～⑬	△	PRE-TIN	PRE-TIN	GREEN	2-171882-4
①～⑬	△	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	2-171882-1
①～⑬	△	PRE-TIN	PRE-TIN	NATURAL	2-171882-1
①～⑬	△	PRE-TIN	PRE-TIN	GRAY	171882-6
①～⑬	△	PRE-TIN	PRE-TIN	GREEN	171882-4
①～⑬	△	PRE-TIN	PRE-TIN	BLACK	171882-2
①～⑬	△	PRE-TIN	PRE-TIN	NATURAL	171882-1
GOLD PL. POSITION No. 金めっき位置番号		SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
		CONTACT FINISH コンタクト仕上			

TOLERANCE UNLESS OTHERWISE SPECIFIED. 公差
0<≦ 10 : ±0.2
10<≦ 30 : ±0.25
30<≦ 100 : ±0.3
ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SHINOHARA	31AUG07	TE Connectivity	
		CHK K. BETSUI	31AUG07		
DIMENSIONS: 単位: 寸法	TOLERANCES UNLESS OTHERWISE SPECIFIED. 公差	APVD K. BETSUI	31AUG07	NAME 名称	13POSITION H TYPE CAP HOUSING MULTI-INTERLOCK CONNECTOR WIRE TO PCB
		PRODUCT SPEC 製品規格	SEE NOTE 4		
		APPLICATION SPEC 取付適用規格			
MATERIAL 材料	FINISH 仕上	WEIGHT	—	SIZE 寸法	CAGE CODE 100779
HSG: 66 NYLON CONTACT: BRASS	SEE TABLE	CUSTOMER DRAWING	SCALE 尺度	2:1	SHEET 1 OF 1