

Line Conditioner / AVR System - Automatic voltage regulator / power conditioner / AC surge suppressor

MODEL NUMBER: LR1000



Description

Tripp Lite's LR1000 automatic voltage regulation system offers complete protection from brownouts, overvoltages and transient surges for computers, printers, fax machines and more. Transformer-based voltage correction circuits maintain usable 220-240V nominal AC output during brownouts as low as 168V and overvoltages to 278V. Network grade equipment protection offers AC surge and noise suppression. Supports heavy loads up to 1000 watts. Includes 4 protected outlets (2 x 5-15R; 2 x C13), 2m-line cord and 7 diagnostic LEDs that display incoming voltage level, surge protection status and line fault conditions.

Features

- Maintains usable 220-240V nominal output during brownouts as low as 168V and overvoltages as high as 278V
- 1000 watts output power rating supports heavy 220-240V loads up to 4 amps
- Network grade surge suppression
- EMI/RFI noise filtering
- 7 diagnostic LEDs indicate input voltage levels, surge suppression status and line fault conditions
- 2 protected NEMA5-15R and 2 C13 outlets
- 2m detachable AC power cord with standard NEMA5-15P input plug

Specifications

OUTPUT	
Nominal Output Voltage(s) Supported	230V
Output (Watts)	1000
Outlet Quantity / Type	4 (2 C13, 2 NEMA 5-15R)

Highlights

- Automatically adjusts low or high voltage without the aid of a battery
- 1000 watts continuous
- 2 NEMA 5-15R and 2 C13 outlets
- Includes a uniplug adapter

Applications

- Maintains usable output voltage during severe brownouts and overvoltages for printers, fax machines, computers, audio/video equipment, CAD/CAM/CAE workstations, network nodes, file servers, phone systems, point-of-sale terminals, and other applications requiring steady input power.

Package Includes

- LR1000 Line Conditioner
- UNIPLUG Plug Adapter
- International Ground Pin Adapter
- Optional 2m C13-to-NEMA 5-15P input cord
- Instruction manual and warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Number of Outlets	4
Outlet Details	Includes 1 uniplug adapter that converts one of the built-in outlets to accept a variety of country specific plug types
INPUT	
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
UPC ASSIGNMENT	
Unit Carton UPC#	037332040152
LEDS ALARMS & SWITCHES	
Front Panel LEDs	7 LEDs show incoming voltage status, protection present and line fault conditions
PHYSICAL	
Shipping Weight (lbs.)	9.00
Shipping Weight (kg)	4.08
Unit Dimensions (hwd / in.)	6.75 x 5.75 x 6.75
Unit Dimensions (hwd / cm)	17.15 x 14.61 x 17.15
Material of Construction	Plastic
Form Factors Supported	Box-shaped power tap format
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.