


SUPER THIN SMD CHIP LED 1608(0603)



UNIT : MM(INCH)
TOLERANCE : ± 0.1 [± 0.004] UNLESS OTHERWISE NOTED

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @20mA		Viewing Angle
			Min.	Typ.	2 θ 1/2
APT1608NW	PURE ORANGE (GaAsP/GaP)	WHITE DIFFUSED	5	12	120°
APT1608QYW	SUPER BRIGHT GREEN (GaP)	WHITE DIFFUSED	3	12	120°
APT1608QGW	SUPER BRIGHT GREEN (GaP)	WHITE DIFFUSED	3	12	120°
APT1608PGW	PURE GREEN (GaP)	WHITE DIFFUSED	2	5	120°
APT1608PYW	PURE YELLOW (GaAsP/GaP)	WHITE DIFFUSED	3	8	120°
APT1608SRWPRV	SUPER BRIGHT RED (GaAlAs)	WHITE DIFFUSED	40	70	120°
APT1608SEW/E	HYPER ORANGE (InGaAlP)	WHITE DIFFUSED	60	200	120°
APT1608SEW	HYPER ORANGE (InGaAlP)	WHITE DIFFUSED	80	200	120°
APT1608SYW	SUPER BRIGHT YELLOW (InGaAlP)	WHITE DIFFUSED	40	60	120°
APT1608MBW	BLUE (GaN)	WHITE DIFFUSED	2	8	120°

APPROVED:

J. Chuang

CHECKED:

J. Chao

DRAWN :

L.N. Sheu

SCALE :

10 : 1

DATA NO. : F2681

DATE : DEC/23/1999