

AULT SPECIFICATIONS

12-20 VA Wall Plug Series

INPUT

Voltage	120 VAC
Line Frequency	60 Hz
Configuration	North American Wall Plug, No Ground

OUTPUT

<i>Model Number</i>	<i>Rated Output Volts AC</i>	<i>Output Current Amps</i>	<i>Max VA</i>
T48-052500-A000G	5	2.50	12.5
T48-062500-A000G	6	2.50	15.0
T48-072500-A000G	7	2.50	17.5
T48-082500-A000G	8	2.50	20.0
T48-092100-A000G	9	2.10	18.9
T48-102000-A000G	10	2.00	20.0
T48-120900-A000G	12	0.90	20.0
T48-121667-A000G	12	1.67	20.0
T48-151333-A000G	15	1.33	20.0
T48-161250-A000G	16	1.25	20.0
T48-181111-A000G	18	1.11	20.0
T48-201000-A000G	20	1.00	20.0
T48-220909-A000G	22	0.91	20.0
T48-240700-A000G	24	0.70	16.8
T48-240833-A000G	24	0.83	20.0

ELECTRICAL

Topology	Step Down AC/AC Transformer
Dielectric Withstand	1500 VAC primary-secondary
Protection	Current, Thermal or Energy Limiting
EMI	Meets FCC Class B
CE	NA

SAFETY APPROVALS

UL1310, CSA22.2-223

ENVIRONMENTAL

Operating Temperature	0° to 40° C with no derating
Storage Temperature	-30° to +85° C
Relative Humidity	5% to 95% non-condensing
Altitude	0 - 10,000 feet
Cooling	Convectional non-vented case

MECHANICAL

Case and Dimensions	T48 - North American Wall Plug 64 L X 57 W X 50 H (mm) 2.5 L X 2.2 W X 2.0 H (in)
Case Material	Black 94V1 Polycarbonate
Weight	17 ounces, 475 grams, (excluding cord)
Cord and Connectors	6 ft., 2 Conductor, 22-24 AWG, Ault #3 Connector Other connectors are also available

WARRANTY

1 Year