




DIN 912

ISO 4762

Standard withdrawn



BN 611

Hex socket head cap screws

partially threaded

Stainless steel A2

- ~UNI 5931
- ~ČSN 021143



The commercial quality of steel grades A2 and A4 is property class 70 (tensile strength 700 N/mm²). Strength of the screw is indicated by the head marking and defined by the applicable product standard.

Article#	d ₁	d ₂	b	k max.	s	t min.	L
1233165	M3	5,5	18	3	2,5	1,3	25
1111345							30
1208101							35
1420429							40
1421913	M4	7	20	4	3	2	30
1111388							35
1111396							40
1111965							45
1111973							50
5519305							60
1233327	M5	8,5	22	5	4	2,5	30
1421921							35
1421948							40
1112368							45
1112376							50
1420437							55
1112384							60
1112392							70
1112449							80
3143347							90
3143350							100
1421956	M6	10	24	6	5	3	35
1233408							40
1113100							45
1421964							50

Article#	d ₁	d ₂	b	k max.	s	t min.	L
1420445	M6	10	24	6	5	3	55
1113119							60
1055380							65
1113127							70
1055399							(75)
1113135							80
3092240							(85)
1129627							90
1208128							100
1488651							110
1488678							120
1488686							130
1488694							140
1488708							150
1233475	M8	13	28	8	6	4	40
1113194							45
1233483							50
1169440							55
1421972							60
1055402							65
1113216							70
1055410							(75)
1113291							80
1113305							90
1113313							100
1488716							110
1113321							120
1488724							130
1488732							140
1488740							150
5522637							160
1113348	M10	16	32	10	8	5	45
1233556							50
1169459							55
1421980							60
1412035							65
1113356							70
1412043							(75)
1113364							80
1113402							90
1113410							100

Article#	d ₁	d ₂	b	k max.	s	t min.	L
1488759	M10	16	32	10	8	5	110
1113429							120
1488767							130
1488775							140
1488783							150
1169467	M12	18	36	12	10	6	55
1422049							60
1412051							65
1113453							70
1412086							(75)
1113461							80
1113526							90
1113534							100
1488791							110
1113542							120
1488805							130
1488813							140
1488821							150
1412094	M16	24	44	16	14	8	65
1113577							70
1412108							(75)
1113585							80
1113666							90
1114093							100
1488848							110
1114107							120
1488856							130
1488864							140
1488872							150
8311098							160
1114174	M20	30	52	20	17	10	80
1114182							90
1114190							100
3092241							110
1114204							120
1114212							140
1114220							160
1114239							180
1114247							200