


LOC	DIST	REVISIONS				
CE	16	P	LTR	DESCRIPTION	DATE	APVD
		C		REV PER EC OB60-0059-03	30SEP03	JH

1. DIMENSIONS IN [] ARE IN INCHES
- 2

MAXIMUM CONNECTOR LOSS IS EQUAL TO 0.50 dB PLUS CABLE ATTENUATION.



0.52	10.0±0.15 [393.7±6]	1-1435725-0
0.52	7.0±0.08 [275.6±3]	1435725-7
0.51	5.0±0.08 [196.9±3]	1435725-5
—	—	—
0.50	3.0±0.05 [118.1±2.0]	1435725-3
0.50	2.0±0.05 [78.7±2.0]	1435725-2
0.50	1.0±0.05 [39.4±2.0]	1435725-1
CONNECTOR LOSS (dB) 2		L
		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
METERS ■ [INCHES]

MATERIAL —

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH —

DWN W SOURBEER 21MAR03
CHK J HOFFER 21MAR03
APVD J APGAR 21MAR03
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —
CUSTOMER DRAWING

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME

CABLE ASSEMBLY, FIBER OPTIC,
AMPTRACS, SC TO SC, DUPLEX, XG, 50um

SIZE A2
CAGE CODE 00779
SCALE NTS

DRAWING NO

C=1435725

RESTRICTED TO

—

SHEET 1 OF 1

REV C

AMP 1471-9 REV 23FEB95