

For the ultimate performance and versatility in a lightweight package with superior maneuverability, the 3102-EU is the perfect choice. With all ball bearing construction, you get longer lasting life and advanced durability, along with a composite grip for superior ergonomics and comfort. Use this powerful die grinder in various applications including porting, weld breaking, deburring, polishing, and grinding, just to name a few.

- ◆ Powerful 0.25 kW (0.33 hp) motor.
- ◆ Lightweight yet durable design.
- ◆ All ball bearing construction.
- ◆ Safety release throttle.
- ◆ Positive grip collet chuck.
- ◆ Ergonomic and durable composite housing.
- ◆ Multi-positional head.
- ◆ Supplied with both 6 mm and 1/4 in collets as standard for all types of accessories.