



## FEATURES:

- Model 5117 Mates to Model # 5109 straight cord female plug.
- Model 5130 Mates to Model # 5125 straight cord female plug.
- Wall or Floor mount receptacle.
- Model 5117 will accept standard 3 pin XLR female plugs.
- Model 5130 will accept standard 5 pin XLR female plugs.
- Durable Zinc Alloy housing.
- Model 5117 Accepts up to 14 AWG.
- Model 5130 Accepts up to 18 AWG.

## MATERIALS:

Housing: Zinc Alloy with a nickel finish

Contacts: Bronze with a Tin finish

Ground Tag: Steel

Insulator: Black Polyester

## RATINGS:

Operating Voltage: 133 VRMS/DC

Current: 15 Amperes.

## ORDERING INFORMATION: Models 5117, 5130

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02"$  (.51 mm), .xxx =  $\pm .005"$  (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA