

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0022023033
Status: Active
Overview: ffc_fpc_throughhole
Description: 2.54mm (.100") Vertical, Non-ZIF, Low Profile Receptacle, 3 Circuits

Documents:	
3D Model	Product Specification PS-5229-005 (PDF)
Drawing (PDF)	Product Specification PS-5229-006 (PDF)
Product Specification PS-5229-001 (PDF)	Product Specification PS-5229-007 (PDF)
Product Specification PS-5229-002 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family FFC/FPC Connectors
Series 5229
Overview ffc_fpc_throughhole
Product Name N/A

Physical

Circuits (Loaded) 3
Contact Position N/A
Entry Angle Vertical
Flammability 94V-0
Mated Height 6.50mm (.256")
Number of Rows 1
Orientation Vertical
PC Tail Length 3.60mm (.142")
PCB Retention None
Packaging Type Tray
Pitch - Mating Interface 2.54mm (.100")
Pitch - Termination Interface 2.54mm (.100")
Polarized to PCB No
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole
Wire/Cable Type FFC/FPC

Electrical


Current - Maximum per Contact 0.5A, 1A
Voltage - Maximum 200V

Material Info

Old Part Number 5229-03CPB

Reference - Drawing Numbers

Product Specification PS-5229-001, PS-5229-002, PS-5229-005,
PS-5229-006, PS-5229-007
Sales Drawing SD-5229-NCPB



EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
5229Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-02-3033](#)