

608 SERIES FOR 8mm MOUNTING HOLE

PART NO.	COLOR	V _F	mA	mcd†	FIG.
608-1131-110	R	2	15	20	1
608-1231-110	G	2	15	15	1
608-1331-110	Y	2	15	4	1
608-3131-110	R	2	15	20	2
608-3231-110	G	2	15	15	2
608-3331-110	Y	2	15	4	2

SNAP-IN

PART NO.	COLOR	V _F	mA	mcd†	FIG.
608-1132-220	R	6	15	20	3
608-1232-220	G	6	15	20	3
608-1332-220	Y	6	15	10	3
608-1132-230	R	12	15	20	3
608-1232-230	G	12	15	20	3
608-1332-230	Y	12	15	10	3
608-2132-220	R	6	15	20	4
608-2232-220	G	6	15	20	4
608-2332-220	Y	6	15	10	4
608-2132-230	R	12	15	20	4
608-2232-230	G	12	15	20	4
608-2332-230	Y	12	15	10	4

Housing Material: Polycarbonate matching color of LED

609 SERIES FOR 9mm MOUNTING HOLE

PART NO.	COLOR	V _F	mA	mcd†	FIG.
609-1112-120	R	6	15	20	5
609-1212-120	G	6	15	15	5
609-1312-120	Y	6	15	4	5
609-1112-130	R	12	15	20	5
609-1212-130	G	12	15	15	5
609-1312-130	Y	12	15	4	5
609-2112-120	R	6	15	20	6
609-2212-120	G	6	15	15	6
609-2312-120	Y	6	15	4	6
609-2112-130	R	12	15	20	6
609-2212-130	G	12	15	15	6
609-2312-130	Y	12	15	4	6

Housing Material: Chrome Plated Brass

610 SERIES FOR 10mm MOUNTING HOLE

PART NO.	COLOR	V _F	mA	mcd†	FIG.
610-3132-120	R	6	10	250	7
610-3232-120	G	6	10	15	7
610-3332-120	Y	6	10	12	7
610-4132-120	R	6	10	250	8
610-4232-120	G	6	10	15	8
610-4332-120	Y	6	10	12	8

Housing Material: Black Polycarbonate

FIG. 1




FIG. 2




FIG. 3




FIG. 4




FIG. 5




FIG. 6




FIG. 7





FIG. 8



† mcd intensity of LED

Dimensions in mm [inches]