

Indicator Lights - Sealed to IP67

Colours and voltages:

 Neon	Available with Red, Amber, Green or Clear lenses 200/250V (marked 230V)
 LED - DC	Red, Yellow, Green LED with resistor for 12V dc, 24V dc
 LED - AC	Red, Yellow, Green, Blue 110-230V ac operation.

- ▶ IP67 Panel Sealing
- ▶ Supplied complete with gaskets/'O' rings
- ▶ Neon, LED, mains LED or filament lamp
- ▶ Bezel sizes from 7.6 to 22.9mm diameter
- ▶ Red, amber, green, blue and clear lenses
- ▶ Red, yellow, green, blue and white LEDs
- ▶ Wide choice of styles




KEA

RoHS

RoHS compliant

To create a catalogue number:

Refer to the 2 columns below (terminal and type), then state: Lens colour, voltage and whether neon, LED or filament lamp

TERM	TYPE	PANEL	ILLUMINATION OPTIONS	DIMENSIONS (mm)
L 	(L) 1041 OS Chrome bezel  	 6.3  5.3 max	 DC  AC	 9.9 4.5  Ø9.5
C 6.3 	(C) 0275 OS Chrome bezel  	 10.0  11.5 max	  DC  AC	 22.2 32.0 3.5 32.2  Ø15.6
C 6.3 	(C) 0277 OS Chrome bezel  	 10.0  11.5 max	  DC  AC	 14.9 3.3 8.3 53.7 32.2  Ø14.6