

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- PDF-NET-ACCESS C ..
- Specification Sheets
- PDF-Net-Access E ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Net-Access E ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips 

☒ Text Search: 'CN182CNUU'

Your search criteria matched only one product, shown below

CN182CNUU



- 42 available rack spaces
- Inset frame posts creating large and accessible vertical pathways for routing cables
- Modular cable management fingers easily mount to the front and/or back of all four cabinet posts
- Designed with the use of CFD (Computational Fluid Dynamics) analysis and thermal lab testing to optimize the thermal performance of network switches requiring side-to-side airflow
- Innovative, fully integrated, electrically bonded cabinet with a single ground connection to guard against EMI and ESD, and provide a safe current path to ground
- Accommodates equipment mounting depths up to 25.9" (658mm)
- Four adjustable equipment mounting rails - available in cage nut or #12-24 threaded with printed rack space identification
- Doors include keyed swing handles
- Side panels include keyed pushbutton latches
- Durable black polyester epoxy powder coat finish

- 2500 lbs. (1134 kg) load rating
- Cabinet ships assembled, one per pallet
- For the complete grounding solution, see the StructuredGround™ Kits for Cabinets.

▪ Part Number	CN182CNUU
▪ RoHS Compliancy Status	Compliant
▪ Part Description	42 available rack spaces. Cabinet frame with top panel. Dual hinge perforated front door opens to the left or right. Split perforated rear doors open in the middle to minimize door swing footprint. Two sets of cage nut rails. Dimensions: 31.5"W (800mm) x 48.9"D (1242mm) x 78.8"H (2000mm)
▪ Color	Black
▪ Depth (In.)	48.9
▪ Depth (mm)	1242
▪ Height (In.)	78.8
▪ Height (mm)	2000
▪ Width (In.)	31.5
▪ Width (mm)	800
▪ No. of Rack Spaces	42
▪ Pricing Description	42 RU x 32"W x 48"D Net-Access Cabinet Front Dual Hinge Door, Rear Split Doors, (2) Side Panels, Cage Nut Rails — Numbers Up
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="button" value=""/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.