


**Model 73063**  
**MMCX Plug to MMCX Plug, RG316/U**

*Model 73063*  
*MMCX Plug to MMCX Plug, RG316/U*

Snap-on coupling and micro-miniature size for fast connect and disconnect where space is limited

**Features**

- DC - 3GHz bandwidth.
- Connectors allow rotation of 360° for layout flexibility.
- Non-slotted contact design for low RF leakage.
- Perfect for applications where space, weight, performance and ease of assembly are required.

**Materials****MMCX Male Connectors:**

Center Contact: Phosphor Bronze, Gold Plated  
Connector Body: Brass, Gold Plated  
Crimp Ferrule: Copper, Nickel Plated  
Insulators: PTFE

**Specifications**

|                              |                                               |
|------------------------------|-----------------------------------------------|
| <b>Cable Type</b>            | RG316/U                                       |
| <b>Impedance</b>             | 50Ω                                           |
| <b>Frequency Range</b>       | DC - 3GHz                                     |
| <b>Insulation Resistance</b> | ≥ 500 MΩ                                      |
| <b>Insulator Withstand</b>   | 500V                                          |
| <b>Temperature Range</b>     | -55° C to +155°C<br>(-67°F to +311°F)         |
| <b>Jacket</b>                | FEP                                           |
| <b>Cable O.D.</b>            | 0.098" (2.5mm)                                |
| <b>Center Conductor (mm)</b> | 7 x .18 silver coated<br>copper covered steel |

**Ordering Information**

Model: **73063**

Cable Designator: **BB** = RG316/U

Standard Lengths: **6", 12", 24", 36"**

- 6" ± .118" (152mm ± 3mm)
- 12" ± .157" (305mm ± 4mm)
- 24" ± .275" (610mm ± 7mm)
- 36" ± .394" (914mm ± 10mm)

Ordering Example: **73063-BB-24**, Cable is RG316/U with length of 24" (610mm)

**USA:** Sales: 800-490-2361  
Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
Fax: 425-446-5844  
**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500  
**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.