

REDINGTON COUNTERS, INC.
P.O. Box 608, 130 Addison Road, Windsor, CT 06095
Toll Free: (860) 688-6205 • Fax: 860/688-1591
E-Mail: Info@RedingtonCounters.com • Website: www.RedingtonCounters.com

Item # 711-0150, 115VAC/60Hz, 2.28 inch Dia., Flush mount, screw termination



115VAC/60Hz, 2.28 inch Dia., Flush mount, screw termination

These 7 figures, AC hour meters with running indicators, offer crisp, distinctive styling for many panel applications. Available in square and round bezel, flush mount or three-hole round panel mount. Each is light-weight, low power, and carry UL, CSA and CE approvals.

SPECIFICATIONS

Model No.	711
Mounting	Panel (mounting hardware included)- Flush Mount
Reset	Non-reset
Termination	1/4 inch (6.3mm) spade terminals with removable screws.
Display	7 figures, 0.14 inch high (3.6mm), 99999.99 hours
Display Height	0.14 Inch
Display Height	3.6 mm
No. of Digits	7
Records	99999.99 hours
Input Voltage	115 VAC 60 Hz ± 10%
Power	3 watts
Operating Temperature	-22 to +158 °F
Operating Temperature	-30 to +70 °C
Weight	2 oz
Weight	57 gm
Panel Cutout	1.81 Sq. Inch 1.99 Dia. Inch
Panel Cutout	46 Sq. mm 50 Dia. mm
Approvals	UL Recognized and CSA Certified. CE Approved

Stock Availability	Yes
--------------------	-----