

Anna-40-7 series



Ordering number C11716

Description C11716_Anna-40-7-S-OSL

Family	Anna-40-7	FWHM	degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/Im	-
Color	Transparent	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



Ordering number C11717

Description C11717_Anna-40-7-M-OSL

Family	Anna-40-7	FWHM	degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/Im	-
Color	Transparent	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



Ordering number C11718

Description C11718_Anna-40-7-W-OSL









Family	Anna-40-7	FWHM	degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/Im	-
Color	Transparent	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

D

C

B

A

Anna-3Anna-4Anna-5Anna-6Anna-7

Material: PMMA

Versions:

Anna-3-S
Anna-3-M
Anna-3-W
Anna-4-S
Anna-4-M
Anna-4-W
Anna-5-S
Anna-5-M
Anna-5-W
Anna-6-S
Anna-6-M
Anna-6-W
Anna-7-S
Anna-7-M
Anna-7-W

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.

L
T
F
Fe
e
i
iN
nd
h

DRAWING TITLE

Datasheet Anna40-series Lens

DRAWN BY

p

DATE

12.10.2010

CHECKED BY

s

n

DATE

12.10.2010

DESIGNED BY

hh

DATE

30.07.2010

SIZE

A4

DRAWING NUMBER

-

REV

1

SCALE

1:1

WEIGHT (g)

SHEET

1/1

D

A