


HONEYWELL PART NUMBER
1SM2
PRODUCT CODE TWA0200

REV	DOCUMENT	CHANGED BY	CHECK
A	0034444	JA 12OCT07	PSR



RELEASE NO.:

REPLACES

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH	DRAWN	JA	12OCT07	Honeywell			
OPERATING FORCE-----3-5 OZ.		CONTACT ARRANGEMENT SPDT			TOLERANCES UNLESS NOTED:	CHECK	PSR	12OCT07				
RELEASE FORCE-----1 OZ. MIN.		30 VOLTS DC RATING			NO PLACE X ± 0.040	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE			
DIFFERENTIAL TRAVEL-----.004 MAX.		SEA LEVEL 50,000 FT			ONE PLACE .X ± 0.030							
OVERTRAVEL-----.010 MIN.		INDUCTIVE 3 AMP 2.5 AMP			TWO PLACE .XX ± 0.015				SIZE	TYPE	DRAWING NAME	REV
		RESISTIVE 5 AMP 5 AMP			THREE PLACE .XXX ± 0.005	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			B	I	1SM2	14
		MAXIMUM INRUSH 24 AMP			FOUR PLACE .XXXX ± 0.0005				SCALE -			
		APPROVALS KEMA, CE 5A, 250V ~ T85 1E4 UL, CSA 5A, 250 VAC ~ BRAND L4			ANGLES ± 2	RASTER			WEIGHT .006 LB MAX			
					THIRD ANGLE PROJECTION				SHEET			1 OF 1