



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove)    [Search Tips](#)    Within Results

**Text Search: 'HSTTRA50-48-5'**

Your search criteria matched only one product, shown below

## HSTTRA50-48-5



- Dual Wall Polyolefin DAMP-SHRINK<sup>TM</sup>Heat Shrink Tubing in 4 ft (1.2M) Pieces
- For damp locations
  - Semi-rigid tubing
  - Adhesive inner wall seals and protects components from moisture and corrosion
- 
- Provides a rugged seal against the elements
  - Material Type: Polyolefin Cross -Linked with adhesive
  - Ratio: 2.5:1
  - Temperature Range: -67°F to 230°F (-55°C to 110°C)
  - Voltage Rating: 600V
  - Mil Spec: AMSDTL-23053/4 Class 1

|                                        |                                                             |
|----------------------------------------|-------------------------------------------------------------|
| Part Number                            | HSTTRA5048-5                                                |
| RoHS Compliancy Status                 | Compliant                                                   |
| Part Description                       | Dual Wall Adhesive Lined SemRigid Heat Shrink               |
| Material                               | Polyolefin cross-linked with adhesive.                      |
| Color                                  | Black                                                       |
| Military Specification                 | AMS-DTL-23053/4 Class 1                                     |
| Length (ft.)                           | 4                                                           |
| Length (m)                             | 1.2                                                         |
| Flammability Rating                    | Outer Wall Flame Retardant                                  |
| Max. Recovered I.D. (In.)              | .195                                                        |
| Max. Recovered I.D. (mm)               | 5.0                                                         |
| Min. Expanded I.D. (In.)               | .500                                                        |
| Min. Expanded I.D. (mm)                | 12.7                                                        |
| Nominal Diameter (In.)                 | .500                                                        |
| Nominal Diameter (mm)                  | 12.7                                                        |
| Nominal Recovered Wall Thickness (In.) | .059                                                        |
| Nominal Recovered Wall Thickness (mm)  | 1.5                                                         |
| Pricing Description                    | Heat Shrink Thin SemRigid, Adhesive .50"(12.7mm) Dia, Black |
| Shrink Ratio                           | 2.5:1                                                       |
| Temperature Range                      | -67°F to 230°F (55°C to 110°C)                              |
| Min. Order UOM                         | PC                                                          |
| Min. Order Qty.                        | 5                                                           |
| BOM Qty. (# of Pkgs.)                  | <input type="text" value="0"/>                              |
| Add to Favorite Product List           |                                                             |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.