





(2,54 mm) .100" (ICF)

(1,27 mm) .050" (PLCC)

ICF, PLCC SERIES



ICF-624-S-O



PLCC-068-F-A

# SMT DIP & CHIP CARRIER SOCKETS

## SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?ICF](http://www.samtec.com?ICF)

### Insulator Material:

Black LCP



### Contact Material:

BeCu

### Plating:

Au or Sn over

50µ" (1,27 µm) Ni

### Current Rating:

1A per contact

### Operating Temp Range:

-55°C to +125°C

### Contact Resistance:

10 mΩ

### Insertion Depth:

(2,54 mm) .100" to

(3,81 mm) .150"

### Insertion Force/Contact:

5 oz (1,39 N) average

### Withdrawal Force/Contact:

4 oz (1,11 N) average

### RoHS Compliant:

Yes

### Processing:

#### Lead-Free Solderable:

Yes

#### SMT Lead Coplanarity:

.006" (0,15 mm) max

## ICF

## ROW SPACING & NO. OF CONTACTS



## PLATING OPTION

## TAIL OPTION

## OTHER OPTION



Specify from chart below



| "-XXX" | Row Space    | No. of Contacts |
|--------|--------------|-----------------|
| -308   | .300 (7,62)  | 08              |
| -314   |              | 14              |
| -316   |              | 16              |
| -318   |              | 18              |
| -320   |              | 20              |
| -324   | .600 (15,24) | 24              |
| -328   |              | 28              |
| -624   |              | 24              |
| -628   |              | 28              |
| -632   |              | 32              |
| -640   |              | 40              |


**-S**  
=30µ"  
(0,76 µm)  
Gold on contact,  
Matte Tin on tail

**-T**  
= Matte Tin

**-I**  
=Tails In



**-O**  
=Tails Out



**-TR**  
=Tape & Reel Packaging

**Note:**  
Some sizes, styles and options are non-standard, non-returnable.

## SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?PLCC](http://www.samtec.com?PLCC)

### Insulator Material:

Black Liquid



### Contact Material:

BeCu

### Plating:

Sn or Au over

50µ" (1,27 µm) Ni

### Current Rating:

1A per contact

### Operating Temp Range:

-55°C to +105°C

### Contact Resistance:

10 mΩ

### RoHS Compliant:

Yes

### Processing:

#### Lead-Free Solderable:

Yes

#### Lead Coplanarity:

Less than 52 leads=

.006" (0,15 mm) max;

52 leads and more=

.008" (0,20 mm) max

## PLCC


## NO. OF CONTACTS

## PLATING OPTION

## ALIGNMENT PIN OPTION

## PACKAGE OPTION

-020, -032, -044, -068



\*32 position has  
.040" (1,00 mm) DIA x  
.030" (0,76 mm) high  
standoffs in corners.


| NO. OF PINS | A             | B             | C            | D            |
|-------------|---------------|---------------|--------------|--------------|
| -020        | .600 (15,24)  | .600 (15,24)  | .370 (9,40)  | .370 (9,40)  |
| -032        | .700 (17,78)  | .800 (20,32)  | .470 (11,94) | .570 (14,48) |
| -044        | .900 (22,86)  | .900 (22,86)  | .670 (17,02) | .670 (17,02) |
| -068        | 1.200 (30,48) | 1.200 (30,48) | .970 (24,64) | .970 (24,64) |

**-F**  
=Gold flash on contact,  
Matte Tin on tail


**-T**  
Matte Tin

**-N**  
=No Alignment Pins

**-A**  
=Alignment Pins



**-TR**  
=Tape & Reel Packaging



Leave package option blank for packaging in a tube.

**Note:**  
Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329  
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0  
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292  
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766  
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683

