


D-Series



The D-Series toggle switches are single pole and have ratings up to 20 amps and 1-1/2 horsepower. These switches have a nylon toggle and base, and are also available with integrated wire leads.

- Specifications**
- Certifications*: UL, CSA
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Nylon
 - Actuator Material: Nylon
 - Bushing Material: Polycarbonate

* Due to ongoing technological advances, consult factory for certification specifics.



D	A	22	1	-	P	B	-	B
SERIES	RATING		TERMINATION		TOGGLE STYLE	TOGGLE COLOR¹		
D SINGLE POLE TOGGLE	10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC		0 SOLDER LUG 1 .250TAB (QC) 5 WIRE LEAD		B BAT P PADDLE	B BLACK W WHITE		
CIRCUIT	11 5A 250VAC 10A 125VAC					BUSHING¹		
A ON-NONE-OFF B ON-NONE-ON C ON-OFF-ON	22 10A 250VAC 20A 125VAC 1 1/2HP 125-250VAC					B BLACK W WHITE		
	23 10A 250VAC 20A 125VAC							
	60 3A 250VAC 6A 125VAC 1/4HP 125-250VAC							

NOTES:
Shading indicates standard configurations.
Available with neoprene seal. Consult factory.
1 Custom colors are available. Consult factory.