

Lisa2-Clip16-DD miniature lens for Sharp GM2BB... (Double Dome) series of LEDs



SHARP.



- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F). Lens holder molded of high quality black PC.
- High optical efficiency, up to 90%.
- Integrated holder with small snap clips. See drawing below for more details. Fastening of holder to PCB.
- Very small and compact dimensions: Diameter 9.9 mm, height 6.8 mm.


LENS TYPES

NAME	ORDERING CODE	FWHM Angle
Lisa2-Clip16 Real Spot	FA11085_Lisa2-RS-clip16-DD	$\pm 9^\circ$
Lisa2-Clip16 Medium	FA11075_Lisa2-M-clip16-DD	$\pm 14^\circ$
Lisa2-Clip16 Oval	FA11121_Lisa2-O-clip16-DD	$\sim \pm 5^\circ \times \sim 16^\circ$
Lisa2-Clip16 Wide	FA11076_Lisa2-W-clip16-DD	$\pm 22^\circ$

~ results are based on simulation value.



MEASUREMENT DATA

Relative Intensity of FA11055_Lisa2-RS-Pin-DD





© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of FA10995_Lisa2-M-Pin-DD




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of FA10996_Lisa2-W-Pin-DD



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice