

Fuseholder Open Design, Holder for MSB and 172876, SMD



125 VAC/DC · 7 A (UL/CSA)



Description

- Surface Mount Device

Standards

- UL 4248-1 / UL 512
- CSA C22.2 no. 39

Approvals

- UL File Number: E41738
- CSA File Number: 23151

References

Packaging Details

Fuseholder to [MSB](#); [172876](#)

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)



Technical Data

Fuse-Link	2 x 7 mm
Mounting	PCB
Terminal	Solder SMT
Rated Voltage	125 VAC/DC
Rated current	7 A (UL/CSA)
Degree of Protection	IP 00
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/21 acc. to IEC 60068-1
Material: Socket	Thermoplastic, black, UL 94V-0
Material: Terminals	Tin-Plated Bronze
Unit Weight	0.45 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 , Approvals

Soldering Methods	Reflow
Solderability	245 °C / 3 sec acc. to IEC 60068-2-20, Test Td
Resistance to Soldering Heat	260 °C / 10 sec acc. to IEC 60068-2-20, Test Td
Contact Resistance	< mΩ at 20 mV

Dimension

14 mm



Soldering pads

All Variants

Holder	Order Number
•	7090.9010.xx

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging Unit	.xx = .03 Plastic Bag (100 pcs.)
	.xx = .55 Blister Tape (500 pcs.)
