


Loc	DIST	REVISIONS			
		P	F	ZONE	LTR
AF	50	P	F	ZONE	LTR
				G1	REVISED PER ECR-12-022060
					26DEC12 CX-LL

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2 SLOT ACCEPTS 0.36-0.57 mm [#27-#23] AWG COPPER MAGNET WIRE.
- 3 MATES WITH STANDARD MAG-MATE STYLED POKE-IN TAB TERMINAL.
- 4? 0.002032 [.000080] MIN TIN OVER 0.00127 [.000050] MIN NICKEL.
- 5? 0.002032 [.000080] MIN TIN.



5	HO4 PHOS. BRONZE	1-63551-3
5	1-63551-3	63551-3
4M BRASS	4M BRASS	63551-2
4M BRASS	4M BRASS	63551-1

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON:		DR 8/21/89	NAME	
2 PLC DEC ± -		CHK 8/23/89	AMP INCORPORATED	
3 PLC DEC ± 0.25 [.010]		JR RUTH	Harrisburg, Pa. 17105	
ANGLES ± -		APPD 8/23/89	SPECIAL LEAF CONTACT, 300 SERIES MAG-MATE™	
MATERIAL		DF DECKER		
SEE TABLE		TL SHUTTER		
SEE TABLE		PRODUCT SPEC		
SEE TABLE		108-2012	SIZE GAGE CODE DRAWING NO	
SEE TABLE		APPLICATION SPEC		
SEE TABLE		114-2046		
SEE TABLE		WEIGHT -	SCALE 5:1 SHEET 1 OF 1	

METRIC