


COST-EFFECTIVE RELIABLE SOCKET

(1.27 mm) .050" PITCH • FLE SERIES



FLE

Board Mates:
FTSH, FTS, FW

Cable Mates:
FFMD*, FMTP

***Note:**
Standard FFMD callout will not mate with FLE, SFMC. Must use gold plated callouts. (See drawing on web.)

FLE	-	1	NO. PINS PER ROW	-	01	-	PLATING OPTION	-	DV	-	OPTION
			02 thru 50				-G = 10 μ" (0.25 μm) Gold				-A = Alignment Pin (Metal or plastic at Samtec discretion) (3 positions minimum)

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer

Contact Material:
Phosphor Bronze

Plating:
Au over 50 μ" (1.27 μm) Ni

Current Rating:
2.9 A per pin
(2 pins powered)

Operating Temp Range:
-55 °C to +125 °C


Insertion Depth:
(1.83 mm) .072" to (4.37 mm)

Max Cycles:
100+

PROCESSING


Lead-Free Solderable:
Yes

SMT Lead Coplanarity:
(0.10 mm) .004" max



ALSO AVAILABLE

Other Plating
(MOQ Required)



Note:
Some lengths, styles and options are non-standard, non-returnable.