


EPA1071 thru EPA1074




- Isolation at PBX and Terminals •
- Dual Package Configuration •


Electrical Parameters @ 25°C

PCA Part Number	OCL (mH Min.)	Interwinding Capacitance (pF Max.)	Leakage Inductance (pH Max.)	Turns Ratio (±5%)	Isolation (Vrms)	DCR (Ω Max.)		Schematics
						Pr.L.	Sec.	
EPA1071	1.20 & 1.20	30 & 30	.50 & .50	1:2CT & 1:2CT	1500	.70 & .70	1.2 & 1.2	A
EPA1072	1.20 & 1.20	35 & 35	.50 & .50	1:2CT & 1:1.36	1500	.80 & .80	1.2 & 1.0	C
EPA1073	2.00 & 2.00	45 & 45	.80 & .80	1:2CT & 1:2CT	1500	.70 & .70	1.2 & 1.2	B
EPA1074	1.20 & 1.20	30 & 30	.55 & .55	1CT:2CT & 1:1	1500	.70 & .70	1.2 & .70	D

Schematics



Package



Dimensions

Dim.	(Inches)			(Millimeters)		
	Min.	Max.	Nom.	Min.	Max.	Nom.
A	.790	.800	.790	19.91	20.32	20.07
B	.385	.395	.375	9.27	9.79	9.52
C	.230	.290	.240	5.94	6.05	6.10
D	--	--	.800	--	--	15.24
E	.013	.017	.015	.330	.432	.381
F	--	--	.100	--	--	2.54
G	.290	.310	.300	7.37	7.97	7.62
H	.017	.020	.020	.432	.508	.509
I	.200	Typ.	.200	5.09	Typ.	5.09
K	.110	.140	.125	2.79	3.57	3.17